


**SILICONE AND
RUBBER PROFILES
FOR INFLATABLE
SEALS**

34,8

5




SILICONE PROFILES

34,8


5






Profile S1

Item number: 610 025, 610 465
 Material: Silicone, transp., red brown
 Stroke: 1 mm
 Minimum bending radius
 Axial: R 45 mm
 Radial In-/Outside: R 40 mm




Profile S2

Item number: 610 292
 Material: Silicone, transparent
 Stroke: 0,5 mm
 Minimum bending radius
 Axial: R 25 mm
 Radial In-/Outside: R 25 mm




Profile S3

Item number: 610 232
 Material: Silicone, transparent
 Stroke: 2 mm
 Minimum bending radius
 Axial: R 65 mm
 Radial In-/Outside: R 50 mm




Profile S4

Item number: 610 024, 610 405
 Material: Silicone, transp., red brown
 Stroke: 5 mm
 Minimum bending radius
 Axial: R 75 mm
 Radial In-/Outside: R 85 mm




Profile S5

Item number: 610 514
 Material: Silicone, black
 Stroke: 8 mm
 Minimum bending radius
 Axial: R 100 mm
 Radial In-/Outside: R 55 mm




Profile S6

Item number: 610 243
 Material: Silicone, transparent
 Stroke: 3 mm
 Minimum bending radius
 Axial: R 100 mm
 Radial In-/Outside: R 110 mm




Profile S7

Item number: 610 023
 Material: Silicone, transparent
 Stroke: 12 mm
 Minimum bending radius
 Axial: R 160 mm
 Radial In-/Outside: R 115 mm



Profile S8


Item number: 610 079
 Material: Silicone, transparent
 Stroke: 20 mm
 Minimum bending radius
 Axial: R 300 mm
 Radial In-/Outside: R 130 mm



Profile S9


Item number: 610 420
 Material: Silicone, transparent
 Stroke: 4 mm
 Minimum bending radius
 Axial: R 40 mm
 Radial In-/Outside: R 40 mm

Drawings are not to scale.




Profile S10

Item number: 610 241, 610 472
 Material: Silicone, transp., red brown
 Stroke: 8 mm
 Minimum bending radius
 Axial: R 110 mm
 Radial In-/Outside: R 80 mm




Profile S11

Item number: 610 369
 Material: Silicone, red brown
 Stroke: 0,5 mm
 Minimum bending radius
 Axial: R 20 mm
 Radial In-/Outside: R 20 mm




Profile S12

Item number: 610 331, 610 479
 Material: Silicone, transp. / black
 Stroke: 1,5 mm
 Minimum bending radius
 Axial: R 90 mm
 Radial In-/Outside: R 35 mm




Profile S13

Item number: 610 311, 610 412
 Material: Silicone, transp., red brown
 Stroke: 12 mm
 Minimum bending radius
 Axial: R 200 mm
 Radial In-/Outside: R 100 mm




Profile S14

Item number: 610 336
 Material: Silicone, red brown
 Stroke: 0,5 mm
 Minimum bending radius
 Axial: R 35 mm
 Radial In-/Outside: R 35 mm




Profile S15

Item number: 610 384
 Material: Silicone, black
 Stroke: 7 mm
 Minimum bending radius
 Axial: R 100 mm
 Radial In-/Outside: R 40 mm




Profile S16

Item number: 610 617
 Material: Silicone, transparent
 Stroke: 10 mm
 Minimum bending radius
 Axial: R 110 mm
 Radial In-/Outside: R 50 mm



Profile S17


Item number: 610 359
 Material: Silicone, red brown
 Stroke: 0,5 mm
 Minimum bending radius
 Axial: R 35 mm
 Radial In-/Outside: R 35 mm



Profile S18


Item number: 610 339
 Material: Silicone, red brown
 Stroke: 1 mm
 Minimum bending radius
 Axial: R 55 mm
 Radial In-/Outside: R 30 mm

Drawings are not to scale.




Profile S19

Item number: 610 367
 Material: Silicone, red brown
 Stroke: 1 mm
 Minimum bending radius
 Axial: R 65 mm
 Radial In-/Outside: R 55 mm




Profile S20

Item number: 610 351
 Material: Silicone, red brown
 Stroke: 1,5 mm
 Minimum bending radius
 Axial: R 45 mm
 Radial In-/Outside: R 65 mm




Profile S21

Item number: 610 345
 Material: Silicone, red brown
 Stroke: 1 mm
 Minimum bending radius
 Axial: R 120 mm
 Radial In-/Outside: R 50 mm




Profile S22

Item number: 610 329
 Material: Silicone, red brown
 Stroke: 0,5 mm
 Minimum bending radius
 Axial: R 50 mm
 Radial In-/Outside: R 40 mm




Profile S23

Item number: 610 324
 Material: Silicone, transparent
 Stroke: 4 mm
 Minimum bending radius
 Axial: R 130 mm
 Radial In-/Outside: R 55 mm




Profile S24

Item number: 610 388
 Material: Silicone, red brown
 Stroke: 5 mm
 Minimum bending radius
 Axial: R 270 mm
 Radial In-/Outside: R 160 mm




Profile S25

Item number: 610 395
 Material: Silicone, transparent
 Stroke: 0,5 mm
 Minimum bending radius
 Axial: R 45 mm
 Radial In-/Outside: R 90 mm



Profile S26


Item number: 610 399
 Material: Silicone, black
 Stroke: 5 mm
 Minimum bending radius
 Axial: R 115 mm
 Radial In-/Outside: R 45 mm




Profile S27

Item number: 610 400
 Material: Silicone, black
 Stroke: 3 mm
 Minimum bending radius
 Axial: R 96 mm
 Radial In-/Outside: R 80 mm


Drawings are not to scale.




Profile S28
 Item number: 610 418
 Material: Silicone, red brown
 Stroke: 0,4 mm
 Minimum bending radius
 Axial: R 10 mm
 Radial In-/Outside: R 15 mm




Profile S29
 Item number: 610 419
 Material: Silicone, red brown
 Stroke: 2,5 mm
 Minimum bending radius
 Axial: R 80 mm
 Radial In-/Outside: R 175 mm




Profile S30
 Item number: 610 431
 Material: Silicone, red brown
 Stroke: 1,5 mm
 Minimum bending radius
 Axial: R 100 mm
 Radial In-/Outside: R 115 mm




Profile S31
 Item number: 610 434
 Material: Silicone, red brown
 Stroke: 2 mm
 Minimum bending radius
 Axial: R 230 mm
 Radial In-/Outside: R 175 mm




Profile S32
 Item number: 610 435
 Material: Silicone, transparent
 Stroke: 10 mm
 Minimum bending radius
 Axial: R 270 mm
 Radial In-/Outside: R 65 mm




Profile S33
 Item number: 610 436
 Material: Silicone, grey
 Stroke: 5 mm
 Minimum bending radius
 Axial: R 300 mm
 Radial In-/Outside: R 230 mm



Profile S34
 Item number: 610 443, 610 466
 Material: Silicone, transp. black
 Stroke: 8 mm
 Minimum bending radius
 Axial: R 170 mm
 Radial In-/Outside: R 75 mm




Profile S35
 Item number: 610 445
 Material: Silicone, red brown
 Stroke: 0,5 mm
 Minimum bending radius
 Axial: R 15 mm
 Radial In-/Outside: R 15 mm




Profile S36
 Item number: 610 449
 Material: Silicone, red brown
 Stroke: 1,5 mm
 Minimum bending radius
 Axial: R 60 mm
 Radial In-/Outside: R 30 mm

Drawings are not to scale.




Profile S37

Item number: 610 456
 Material: Silicone, transparent
 Stroke: 7 mm
 Minimum bending radius
 Axial: R 190 mm
 Radial In-/Outside: R 85 mm




Profile S38

Item number: 610 461
 Material: Silicone, transparent
 Stroke: 2 mm
 Minimum bending radius
 Axial: R 100 mm
 Radial In-/Outside: R 75 mm




Profile S39

Item number: 610 464
 Material: Silicone, transparent
 Stroke: 2 mm
 Minimum bending radius
 Axial: R 80 mm
 Radial In-/Outside: R 70 mm




Profile S40

Item number: 610 455
 Material: Silicone, red brown
 Stroke: 4 mm
 Minimum bending radius
 Axial: R 100 mm
 Radial In-/Outside: R 55 mm




Profile S41

Item number: 610 480
 Material: Silicone, transparent
 Stroke: 2,5 mm
 Minimum bending radius
 Axial: R 65 mm
 Radial In-/Outside: R 65 mm




Profile S42

Item number: 610 484
 Material: Silicone, red brown
 Stroke: 0,5 mm
 Minimum bending radius
 Axial: R 10 mm
 Radial In-/Outside: R 15 mm




Profile S43

Item number: 610 492
 Material: Silicone, red brown
 Stroke: 18 mm
 Minimum bending radius
 Axial: R 300 mm
 Radial In-/Outside: R 270 mm



Profile S44


Item number: 610 500
 Material: Silicone, transparent
 Stroke: 5 mm
 Minimum bending radius
 Axial: R 170 mm
 Radial In-/Outside: R 140 mm




Profile S45

Item number: 610 511
 Material: Silicone, red brown
 Stroke: 0,5 mm
 Minimum bending radius
 Axial: R 45 mm
 Radial In-/Outside: R 50 mm


Drawings are not to scale.




Profile S46
 Item number: 610 512
 Material: Silicone, transparent
 Stroke: 6 mm
 Minimum bending radius
 Axial: R 115 mm
 Radial In-/Outside: R 60 mm




Profile S47
 Item number: 610 503
 Material: Silicone, transparent
 Stroke: 13 mm
 Minimum bending radius
 Axial: R 260 mm
 Radial In-/Outside: R 215 mm




Profile S48
 Item number: 610 513
 Material: Silicone, transparent
 Stroke: 3 mm
 Minimum bending radius
 Axial: R 90 mm
 Radial In-/Outside: R 50 mm




Profile S49
 Item number: 610 526
 Material: Silicone, red brown
 Stroke: 1 mm
 Minimum bending radius
 Axial: R 45 mm
 Radial In-/Outside: R 35 mm




Profile S50
 Item number: 610 527
 Material: Silicone, transparent
 Stroke: 4 mm
 Minimum bending radius
 Axial: R 150 mm
 Radial In-/Outside: R 175 mm




Profile S51
 Item number: 610 530
 Material: Silicone, red brown
 Stroke: 2 mm
 Minimum bending radius
 Axial: R 75 mm
 Radial In-/Outside: R 95 mm



Profile S52
 Item number: 610 532
 Material: Silicone, red brown
 Stroke: 1 mm
 Minimum bending radius
 Axial: R 55 mm
 Radial In-/Outside: R 60 mm




Profile S53
 Item number: 610 558
 Material: Silicone, grey
 Stroke: 6 mm
 Minimum bending radius
 Axial: R 55 mm
 Radial In-/Outside: R 65 mm




Profile S54
 Item number: 610 566
 Material: Silicone, red brown
 Stroke: 14 mm
 Minimum bending radius
 Axial: R 170 mm
 Radial In-/Outside: R 80 mm

Drawings are not to scale.




Profile S55

Item number: 610 535
 Material: Silicone, red brown
 Stroke: 20 mm
 Minimum bending radius
 Axial: R 260 mm
 Radial In-/Outside: R 160 mm




Profile S56

Item number: 610 582
 Material: Silicone, transparent
 Stroke: 19 mm
 Minimum bending radius
 Axial: R 280 mm
 Radial In-/Outside: R 150 mm




Profile S57

Item number: 610 605
 Material: Silicone, transparent
 Stroke: 10 mm
 Minimum bending radius
 Axial: R 130 mm
 Radial In-/Outside: R 70 mm




Profile S58

Item number: 610 606
 Material: Silicone, transparent
 Stroke: 5 mm
 Minimum bending radius
 Axial: R 50 mm
 Radial In-/Outside: R 45 mm




Profile S59

Item number: 610 608
 Material: Silicone, weiß
 Stroke: 1,5 mm
 Minimum bending radius
 Axial: R 25 mm
 Radial In-/Outside: R 30 mm




Profile S60

Item number: 610 607
 Material: Silicone, transparent
 Stroke: 1 mm
 Minimum bending radius
 Axial: R 40 mm
 Radial In-/Outside: R 30 mm




Profile S61

Item number: 610 574
 Material: Silicone, transparent
 Stroke: 7 mm
 Minimum bending radius
 Axial: R 100 mm
 Radial In-/Outside: R 50 mm



Profile S62


Item number: 610 573
 Material: Silicone, transparent
 Stroke: 7 mm
 Minimum bending radius
 Axial: R 40 mm
 Radial In-/Outside: R 80 mm




Profile S63

Item number: 610 611
 Material: Silicone, transparent
 Stroke: 9 mm
 Minimum bending radius
 Axial: R 50 mm
 Radial In-/Outside: R 80 mm


Drawings are not to scale.




Profile S64
 Item number: 610 621
 Material: Silicone, weiß
 Stroke: 1 mm
 Minimum bending radius
 Axial: R 50 mm
 Radial In-/Outside: R 50 mm




Profile S65
 Item number: 610 619
 Material: Silicone, transparent
 Stroke: 9 mm
 Minimum bending radius
 Axial: R 70 mm
 Radial In-/Outside: R 90 mm




Profile S66
 Item number: 610 635
 Material: Silicone, transparent
 Stroke: 18 mm
 Minimum bending radius
 Axial: R 180 mm
 Radial In-/Outside: R 100 mm




Profile S67
 Item number: 610 632
 Material: Silicone, transparent
 Stroke: 3,5 mm
 Minimum bending radius
 Axial: R 50 mm
 Radial In-/Outside: R 40 mm



Profile S68
 Item number: 610 633
 Material: Silicone, transparent
 Stroke: 2,5 mm
 Minimum bending radius
 Axial: R 30 mm
 Radial In-/Outside: R 40 mm



Profile S69
 Item number: 610 640
 Material: Silicone, transparent
 Stroke: 8 mm
 Minimum bending radius
 Axial: R 120 mm
 Radial In-/Outside: R 45 mm



Profile S70
 Item number: 610 637
 Material: Silicone, blau
 Stroke: 8 mm
 Minimum bending radius
 Axial: R 170 mm
 Radial In-/Outside: R 190 mm


Drawings are not to scale.

RUBBER PROFILES

34,8


5






Profile G1

Item number: 610 442
 Material: EPDM, black
 Stroke: 7 mm
 Minimum bending radius
 Axial: R 115 mm
 Radial In-/Outside: R 65 mm




Profile G2

Item number: 610 474
 Material: EPDM, black
 Stroke: 14 mm
 Minimum bending radius
 Axial: R 95 mm
 Radial In-/Outside: R 35 mm




Profile G3

Item number: 610 458
 Material: EPDM, black
 Stroke: 12 mm
 Minimum bending radius
 Axial: R 120 mm
 Radial In-/Outside: R 40 mm




Profile G4

Item number: 610 473
 Material: EPDM, black
 Stroke: 14 mm
 Minimum bending radius
 Axial: R 115 mm
 Radial In-/Outside: R 40 mm




Profile G5

Item number: 610 483
 Material: EPDM, black
 Stroke: 16 mm
 Minimum bending radius
 Axial: R 435 mm
 Radial In-/Outside: R 230 mm




Profile G6

Item number: 610 469, 610 601
 Material: FKM, NR/SBR, black
 Stroke: 2 mm
 Minimum bending radius
 Axial: R 80 mm
 Radial In-/Outside: R 70 mm




Profile G7

Item number: 610 510
 Material: SBR, black
 Stroke: 3 mm
 Minimum bending radius
 Axial: R 75 mm
 Radial In-/Outside: R 75 mm



Profile G8


Item number: 610 622
 Material: NR/SBR, black
 Stroke: 1 mm
 Minimum bending radius
 Axial: R 45 mm
 Radial In-/Outside: R 50 mm



Profile G9


Item number: 610 496
 Material: EPDM, black
 Stroke: 18 mm
 Minimum bending radius
 Axial: R 380 mm
 Radial In-/Outside: R 220 mm

Drawings are not to scale.




Profile G10

Item number: 610 540
 Material: NBR, black
 Stroke: 7 mm
 Minimum bending radius
 Axial: R 140 mm
 Radial In-/Outside: R 100 mm




Profile G11

Item number: 610 538
 Material: HNBR, black
 Stroke: 1 mm
 Minimum bending radius
 Axial: R 85 mm
 Radial In-/Outside: R 55 mm




Profile G12

Item number: 610 516
 Material: EPDM, black
 Stroke: 15 mm
 Minimum bending radius
 Axial: R 75 mm
 Radial In-/Outside: R 85 mm




Profile G13

Item number: 610424, 610529, 610411
 Material: EPDM, FKM, NBR, black
 Stroke: 10 mm
 Minimum bending radius
 Axial: R 250 mm
 Radial Innen/Außen: R 120 mm




Profile G14

Item number: 610 557
 Material: EPDM, black
 Stroke: 14 mm
 Minimum bending radius
 Axial: R 135 mm
 Radial In-/Outside: R 100 mm




Profile G15

Item number: 610 545
 Material: HNBR, black
 Stroke: 20 mm
 Minimum bending radius
 Axial: R 160 mm
 Radial In-/Outside: R 100 mm




Profile G16

Item number: 610 560
 Material: EPDM, black
 Stroke: 12 mm
 Minimum bending radius
 Axial: R 170 mm
 Radial Innen/Außen: R 100 mm



Profile G17


Item number: 610 581
 Material: EPDM, black
 Stroke: 4 mm
 Minimum bending radius
 Axial: R 40 mm
 Radial In-/Outside: R 40 mm



Profile G18


Item number: 610 600
 Material: EPDM, black
 Stroke: 24 mm
 Minimum bending radius
 Axial: R 260 mm
 Radial In-/Outside: R 90 mm

Drawings are not to scale.




Profile G19

Item number: 610 595
 Material: NR/SBR,
 black
 Stroke: 1 mm
 Minimum bending radius
 Axial: R 25 mm
 Radial In-/Outside: R 30 mm




Profile G20

Item number: 610 599
 Material: EPDM,
 black
 Stroke: 14 mm
 Minimum bending radius
 Axial: R 90 mm
 Radial In-/Outside: R 30 mm




Profile G21

Item number: 610 616
 Material: NBR,
 black
 Stroke: 3 mm
 Minimum bending radius
 Axial: R 40 mm
 Radial In-/Outside: R 50 mm




Profile G22

Item number: 610 636
 Material: EPDM,
 black
 Stroke: 6 mm
 Minimum bending radius
 Axial: R 110 mm
 Radial In-/Outside: R 60 mm



Profile G23

Item number: 610 638
 Material: EPDM,
 black
 Stroke: 5 mm
 Minimum bending radius
 Axial: R 110 mm
 Radial In-/Outside: R 90 mm



Profile G24

Item number: 610 641
 Material: EPDM,
 black
 Stroke: 2 mm
 Minimum bending radius
 Axial: R 50 mm
 Radial In-/Outside: R 40 mm

Drawings are not to scale.



Kruppstrasse 13
41540 Dormagen | Germany
Phone +49 2133 6968 / 6969
Fax +49 2133 63536
post@algummi.de
www.algummi.de